



POL-EKO
Perfect Environment

(+48) 32 453 91 70
info@pol-eko.com.pl
www.pol-eko.com.pl

POL-EKO A. Polok-Kowalska sp.k.
44-300 Wodzisław Śląski
ul. Kokoszycka 172 C

Data sheet


Laboratory Refrigerator CHL 2 Smart



The photo above is for reference only, may show additional options not included in standard equipment. The real appearance, particularly color and structure of the material may differ from the ones presented in the photo.

Advantages of the SMART controller:

- 4,3", clear, full colour touch screen
- LAN, USB ports for data transfer
- multi-segment time and temperature programs
- visual and sound alarm
- internal memory for programs and data storage
- event registry
- user manual for direct download
- Quick change of program parameters
- Alarm Bar
- operating with gloves on



Smart - preview screen



1	99
type	CHL 2 Smart

TECHNICAL DATA

air convection	forced
chamber capacity [l]	150
working capacity [l]	122
controller	microprocessor PID
display	4,3" full colour touch screen

TEMPERATURE

temperature range [°C]	0...+15
temperature resolution every ... [°C]	0,1
temperature fluctuation at 4°C [±/°C]*	0,4
temperature variation at 4°C [±/°C]*	0,7
temperature protection	class 1.0 to DIN 12880 / class 3.2 (option)

CHAMBER


door type	solid / glass or double (option) /4/
interior	
C Smart	stainless steel to DIN 1.4016
CS Smart	stainless steel to DIN 1.4016
P Smart	acid-proof stainless steel to DIN 1.4301
PS Smart	acid-proof stainless steel to DIN 1.4301
housing	
C Smart	powder coated sheet
CS Smart	stainless steel polished
P Smart	powder coated sheet
PS Smart	stainless steel polished

overall dims [mm] /1/

width A	600
height B	900
depth C	650

internal dims [mm]

width D	480
width D'	520
height E	660
depth F	420
depth F'	480
depth G	320
height H	440



shelves (standard max)	3 4
max shelf workload [kg] /2/	10
max unit workload [kg]	30
weight [kg]	54



ELECTRICAL PARAMETERS

voltage**	230V 50-60Hz
nominal power [W]	250
refrigerant	R1234ze / GWP=7
warranty	24 months
manufacturer	POL-EKO
txt_opis_pt	<p>all the above technical data refer to standard units (without optional accessories)</p> <p>* - fluctuation measured in centre of the chamber; in space, variation (K) calculated for chamber as: $K = \frac{+/- (T \text{ average max.} - T \text{ average min.})}{2}$; parameters given for the chamber above the bottom step</p> <p>** - other power supplies on request</p> <p>1 - depth doesn't include 50 mm of power cable, the width does not include the 20 mm of rubber plug</p> <p>2 - on uniformly loaded surface</p> <p>3 - reinforced shelf</p> <p>4 - additional internal glass door</p>
PL typ urządzenia	Laboratory Refrigerator
img_photo	CHL-2-Smart
<p>The photo above is for reference only, may show additional options not included in standard equipment. The real appearance, particularly color and structure of the material may differ from the ones presented in the photo.</p>	
nazwa www pl	Chłodziarka Laboratoryjna CHL 2 Smart
nazwa www EN	Laboratory Refrigerator CHL 2 Smart
nazwa www ES	Refrigerador de Laboratorio CHL 2 Smart
ekran_grafika	chl_smart
	chłodziarki laboratoryjne
	chłodziarki laboratoryjne jednokomorowe
0	1

all the above technical data refer to standard units (without optional accessories)

* - fluctuation measured in centre of the chamber; in space, variation (K) calculated for chamber as: $K = \frac{+/- (T \text{ average max.} - T \text{ average min.})}{2}$; parameters given for the chamber above the bottom step

** - other power supplies on request


1 - depth doesn't include 50 mm of power cable, the width does not include the 20 mm of rubber plug

2 - on uniformly loaded surface

3 - reinforced shelf


4 - additional internal glass door

OPTIONS AND ACCESSORIES



Order number: */C

Internal glass door




Order number: */A

External glass door



Order number: */P INOX

Stainless steel wire shelf INOX



Order number: */PP

Perforated shelf



POL-EKO
Perfect Environment

(+48) 32 453 91 70
info@pol-eko.com.pl
www.pol-eko.com.pl

POL-EKO A. Polok-Kowalska sp.k.
44-300 Wodzisław Śląski
ul. Kokoszycka 172 C



Order number: */PW

Reinforced shelf



Order number: KUW GN*/*

Stainless steel cuvettes



Order number: ST/CHL/SWP ALU

Aluminum drawer with powder coated slides



Order number: ST/CHL/SWP INOX

Stainless steel drawer with powder coated slides




Order number: ST/CHL/SWPN INOX

Stainless steel drawer with stainless steel slides




Order number: QLK*

Castors



Order number: */S or */S INOX

Table with castors




Order number: */ST or */S INOX

Base on castors



Order number: *PLUS

Automatic defrosting function




Order number: GNZ

Internal socket



Order number LabDesk

LabDesk software




Order number: BRT/*/L or IQ/OQ/PQ

Calibration and IQ, OQ, PQ qualification



Order number: */3.2

Over temperature protection 3.2 class according to DIN 12880




Order number: BPP 12

Battery backup for display




Order number: PORT ALARM

Dry alarm contact



Order number: LANK

LAN cable



Order number: OCZ/20

Non-standard access port 20 mm




Bank: ING BŚ o/Wodzisław Śląski | Nr rachunku: 90 1050 1403 1000 0022 0879 5498 | Nr rej. w BDO 000005609
NIP: 647-216-26-87 | REGON: 276111984 | Sąd Rejonowy w Gliwicach, X Wydział Gospodarczy | KRS 0001009595



POL-EKO
Perfect Environment


(+48) 32 453 91 70
info@pol-eko.com.pl
www.pol-eko.com.pl

POL-EKO A.Polok-Kowalska sp.k.
44-300 Wodzisław Śląski
ul. Kokoszycka 172 C




Order number: OCZ/30

Additional access port 30 mm



Order number: OCZ/60

Non-standard access port 60 mm



Order number: OCZ/100

Non-standard access port 100 mm



Order number: KD

Access control