



POL-EKO
Perfect Environment

(+48) 32 453 91 70
info@pol-eko.com.pl
www.pol-eko.com.pl

POL-EKO A. Polok-Kowalska sp.k.
44-300 Wodzisław Śląski
ul. Kokoszycka 172 C

Data sheet


Laboratory Refrigerator CHL 2 Smart



The photo above is for reference only, may show additional options not included in standard equipment. The real appearance, particularly color and structure of the material may differ from the ones presented in the photo.


Advantages of the SMART controller:

- 4,3", clear, full colour touch screen
- LAN, USB ports for data transfer
- multi-segment time and temperature programs
- visual and sound alarm
- internal memory for programs and data storage
- event registry
- user manual for direct download
- Quick change of program parameters
- Alarm Bar
- operating with gloves on



Smart - preview screen



| | |
|--|---|
| 1 | 99 |
| type | CHL 2 Smart |
| TECHNICAL DATA | |
| air convection | forced |
| chamber capacity [l] | 150 |
| working capacity [l] | 122 |
| controller | microprocessor PID |
| display | 4,3" full colour touch screen |
| TEMPERATURE | |
| temperature range [°C] | 0...+15 |
| temperature resolution every ... [°C] | 0,1 |
| temperature fluctuation at 4°C [±/°C]* | 0,4 |
| temperature variation at 4°C [±/°C]* | 0,7 |
| temperature protection | class 1.0 to DIN 12880 / class 3.2 (option) |
| CHAMBER | |
| door type | solid / glass or double (option) /4/ |
| interior | |
| C Smart | stainless steel to DIN 1.4016 |
| CS Smart | stainless steel to DIN 1.4016 |
| P Smart | acid-proof stainless steel to DIN 1.4301 |
| PS Smart | acid-proof stainless steel to DIN 1.4301 |
| housing | |
| C Smart | powder coated sheet |
| CS Smart | stainless steel polished |
| P Smart | powder coated sheet |
| PS Smart | stainless steel polished |
| overall dims [mm] /1/ | |
| width A | 600 |
| height B | 900 |
| depth C | 650 |
| internal dims [mm] | |
| width D | 480 |
| width D' | 520 |
| height E | 660 |
| depth F | 420 |
| depth F' | 480 |
| depth G | 320 |
| height H | 440 |
|  | |
| shelves (standard max) | 3 4 |
| max shelf workload [kg] /2/ | 10 |
| max unit workload [kg] | 30 |
| weight [kg] | 54 |



ELECTRICAL PARAMETERS

| | |
|--|--|
| voltage** | 230V 50-60Hz |
| nominal power [W] | 250 |
| refrigerant | R1234ze / GWP=7 |
| warranty | 24 months |
| manufacturer | POL-EKO |
| txt_opis_pt | <p>all the above technical data refer to standard units (without optional accessories)</p> <p>* - fluctuation measured in centre of the chamber; in space, variation (K) calculated for chamber as: $K = \frac{+/- (T \text{ average max.} - T \text{ average min.})}{2}$; parameters given for the chamber above the bottom step</p> <p>** - other power supplies on request</p> <p>1 - depth doesn't include 50 mm of power cable, the width does not include the 20 mm of rubber plug</p> <p>2 - on uniformly loaded surface</p> <p>3 - reinforced shelf</p> <p>4 - additional internal glass door</p> |
| PL typ urządzenia | Laboratory Refrigerator |
| img_photo | CHL-2-Smart |
| <p>The photo above is for reference only, may show additional options not included in standard equipment. The real appearance, particularly color and structure of the material may differ from the ones presented in the photo.</p> | |
| nazwa www pl | Chłodziarka Laboratoryjna CHL 2 Smart |
| nazwa www EN | Laboratory Refrigerator CHL 2 Smart |
| nazwa www ES | Refrigerador de Laboratorio CHL 2 Smart |
| ekran_grafika | chl_smart |
| | chłodziarki laboratoryjne |
| | chłodziarki laboratoryjne jednokomorowe |
| 0 | 1 |

all the above technical data refer to standard units (without optional accessories)

* - fluctuation measured in centre of the chamber; in space, variation (K) calculated for chamber as: $K = \frac{+/- (T \text{ average max.} - T \text{ average min.})}{2}$; parameters given for the chamber above the bottom step

** - other power supplies on request


1 - depth doesn't include 50 mm of power cable, the width does not include the 20 mm of rubber plug

2 - on uniformly loaded surface

3 - reinforced shelf


4 - additional internal glass door

OPTIONS AND ACCESSORIES



Order number: */C

Internal glass door




Order number: */A

External glass door



Order number: */P INOX

Stainless steel wire shelf INOX



Order number: */PP

Perforated shelf



POL-EKO
Perfect Environment

(+48) 32 453 91 70
info@pol-eko.com.pl
www.pol-eko.com.pl

POL-EKO A. Polok-Kowalska sp.k.
44-300 Wodzisław Śląski
ul. Kokoszycka 172 C



Order number: */PW

Reinforced shelf



Order number: KUW GN*/*

Stainless steel cuvettes



Order number: ST/CHL/SWP ALU

Aluminum drawer with powder coated slides



Order number: ST/CHL/SWP INOX

Stainless steel drawer with powder coated slides




Order number: ST/CHL/SWPN INOX

Stainless steel drawer with stainless steel slides




Order number: QLK*

Castors



Order number: */S or */S INOX

Table with castors




Order number: */ST or */S INOX

Base on castors



Order number: *PLUS

Automatic defrosting function




Order number: GNZ

Internal socket



Order number LabDesk

LabDesk software




Order number: BRT/*/L or IQ/OQ/PQ

Calibration and IQ, OQ, PQ qualification



Order number: */3.2

Over temperature protection 3.2 class according to DIN 12880




Order number: BPP 12

Battery backup for display




Order number: PORT ALARM

Dry alarm contact



Order number: LANK

LAN cable



Order number: OCZ/20

Non-standard access port 20 mm




Bank: ING BŚ o/Wodzisław Śląski | Nr rachunku: 90 1050 1403 1000 0022 0879 5498 | Nr rej. w BDO 000005609
NIP: 647-216-26-87 | REGON: 276111984 | Sąd Rejonowy w Gliwicach, X Wydział Gospodarczy | KRS 0001009595



POL-EKO
Perfect Environment


(+48) 32 453 91 70
info@pol-eko.com.pl
www.pol-eko.com.pl

POL-EKO A.Polok-Kowalska sp.k.
44-300 Wodzisław Śląski
ul. Kokoszycka 172 C




Order number: OCZ/30

Additional access port 30 mm




Order number: OCZ/60

Non-standard access port 60 mm



Order number: OCZ/100

Non-standard access port 100 mm



Order number: KD

Access control