



## Data sheet

print date: 2025-04-28


## Laboratory Refrigerator CHL 2/3 Smart



The photo above is for reference only, may show additional options not included in standard equipment. The real appearance, particularly color and structure of the material may differ from the ones presented in the photo.

### Advantages of the SMART controller:

- 4,3", clear, full colour touch screen
- LAN, USB ports for data transfer
- multi-segment time and temperature programs
- visual and sound alarm
- internal memory for programs and data storage
- event registry
- user manual for direct download
- Quick change of program parameters
- Alarm Bar
- operating with gloves on



Smart - preview screen

**TECHNICAL DATA**

air convection	forced
chamber capacity [l]	150 / 200
working capacity [l]	122 / 163
controller	microprocessor PID
display	4,3" full colour touch screen

**TEMPERATURE**

temperature range [°C]	0...+15
temperature resolution every ... [°C]	0,1
temperature fluctuation at 4°C [±/°C]*	0,4
temperature variation at 4°C [±/°C]*	0,7
temperature protection	class 1.0 to DIN 12880 / class 3.2 (option)

**CHAMBER**

door type	solid / glass or double (option) /4/
-----------	--------------------------------------

**interior**

C Smart	stainless steel to DIN 1.4016
CS Smart	stainless steel to DIN 1.4016
P Smart	acid-proof stainless steel to DIN 1.4301
PS Smart	acid-proof stainless steel to DIN 1.4301

**housing**


C Smart	powder coated sheet
CS Smart	stainless steel polished
P Smart	powder coated sheet
PS Smart	stainless steel polished

**overall dims [mm] /1/**

width A	630
height B	1920
depth C	650

**internal dims [mm]**

width D	480
width D'	520
height E	660 / 860
depth F	420
depth F'	480
depth G	320
height H	440 / 640



shelves (standard   max)	3   4 / 3   4
max shelf workload [kg] /2/	10
max unit workload [kg]	30 / 40
weight [kg]	134



**ELECTRICAL PARAMETERS**

voltage	230V 50-60Hz
nominal power [W]	500
refrigerant	R1234ze / GWP=7
warranty	24 months
manufacturer	POL-EKO®

all the above technical data refer to standard units (without optional accessories)

\* - fluctuation measured in centre of the chamber; in space, variation (K) calculated for chamber as:  $K = \frac{T_{average\ max.} - T_{average\ min.}}{T}$  / 2; parameters given for the chamber above the bottom step

\*\* - other power supplies on request

1 - depth doesn't include 50 mm of power cable, the width does not include the 20 mm of rubber plug

2 - on uniformly loaded surface

3 - reinforced shelf


4 - additional internal glass door

**OPTIONS AND ACCESSORIES**



Order number: \*/C

Internal glass door



Order number: \*/A

External glass door



Order number: \*/AS


glass door with SMART WINDOW option



**INOX**


Order number: \*/P INOX

Stainless steel wire shelf INOX



Order number: \*/PP

Perforated shelf




Order number: \*/PW

Reinforced shelf



Order number: KUW GN\*/\*


Stainless steel cuvettes



**ALU**

Order number: ST/CHL/SWP ALU

Aluminum drawer with powder coated slides



**INOX**

Order number: ST/CHL/SWP INOX

Stainless steel drawer with powder coated slides



**INOX/INOX**


Order number: ST/CHL/SWP INOX

Stainless steel drawer with stainless steel slides



Order number: \*PLUS

Automatic defrosting function




Order number: GNZ

Internal socket



Order number LabDesk

LabDesk software



Order number: BRT\*/L or IQ/OQ/PQ

Calibration and IQ, OQ, PQ qualification



Order number: \*/3.2

Over temperature protection 3.2 class according to DIN 12880



Order number: BPP 12

Battery backup for display




Order number: PORT ALARM

Dry alarm contact



Order number: LANK

LAN cable



Order number: OCZ/20

Non-standard access port 20 mm



Order number: OCZ/30

Additional access port 30 mm



Order number: OCZ/60

Non-standard access port 60 mm



Order number: OCZ/100

Non-standard access port 100 mm



Order number: KD

Access control