



**POL-EKO**  
Perfect Environment

(+48) 32 453 91 70  
info@pol-eko.com.pl  
www.pol-eko.com.pl

**POL-EKO A.Polok-Kowalska sp.k.**  
44-300 Wodzisław Śląski  
ul. Kokoszycka 172 C

## Data sheet

## Peltier-Cooled Incubator ILP 53 Smart



The photo above is for reference only, may show additional options not included in standard equipment. The real appearance, particularly color and structure of the material may differ from the ones presented in the photo.

### Advantages of the SMART controller:

- 4,3", clear, full colour touch screen
- LAN, USB ports for data transfer
- multi-segment time and temperature programs
- visual and sound alarm
- internal memory for programs and data storage
- event registry
- user manual for direct download
- Quick change of program parameters
- Alarm Bar
- operating with gloves on




**Smart** - preview screen



1	49
type	ILP 53 Smart
<b>TECHNICAL DATA</b>	
air convection	forced
chamber capacity [l]	56
working capacity [l]	56
controller	microprocessor PID
display	4,3" full colour touch screen
<b>TEMPERATURE</b>	
temperature range [°C]	0...+70 (max 20°C below ambient temperature)
temperature resolution every ... [°C]	0,1
temperature fluctuation at 37°C [±/°C]*	0,1
temperature variation at 37°C [±/°C]*	0,2
temperature protection	class 2.0 to DIN 12880 / class 3.3 (option)
<b>CHAMBER</b>	
door type	double(5) / door with viewing window (option)
<b>interior</b>	
Smart	acid-proof stainless steel to DIN 1.4301
IG Smart	acid-proof stainless steel to DIN 1.4301
<b>housing</b>	
Smart	powder coated sheet
IG Smart	stainless steel linen finish

**overall dims [mm] /1/**

width A	590
height B	710
depth C	690
<b>internal dims [mm]</b>	
width D	400
height E	390
depth F	360



shelves (standard   max)	2   5
max shelf workload [kg] /2/	25
max unit workload [kg]	50
weight [kg]	69



## ELECTRICAL PARAMETERS

voltage**	230V 50-60Hz
nominal power [W]	500
warranty	24 months
manufacturer	POL-EKO
txt_opis_pt	<p>all the above technical data refer to standard units (without optional accessories)</p> <p>* - fluctuation measured in centre of the chamber; in space, variation (K) calculated for chamber as: <math>K = \pm (T \text{ average max.} - T \text{ average min.}) / 2</math></p> <p>** - other power supplies on request</p> <p>1 - depth doesn't include 50 mm of power cable, the width does not include the 20 mm of rubber plug</p> <p>2 - on uniformly loaded surface</p> <p>3 - reinforced shelf</p> <p>4 - additional internal glass door</p>
PL typ urządzenia	Peltier-Cooled Incubator
img_photo	ILP-53-Smart
<p>The photo above is for reference only, may show additional options not included in standard equipment. The real appearance, particularly color and structure of the material may differ from the ones presented in the photo.</p>	
nazwa www pl	Inkubator z chłodzeniem Peltiera ILP 53 Smart
nazwa www EN	Peltier-Cooled Incubator ILP 53 Smart
nazwa www ES	Incubadora de Refrigeración con el Sistema Peltier ILP 53 Smart
ekran_grafika	st_il_smart
	Inkubatory Z Chłodzeniem Peltiera
0	1

all the above technical data refer to standard units (without optional accessories)

\* - fluctuation measured in centre of the chamber; in space, variation (K) calculated for chamber as:  
 $K = \pm (T \text{ average max.} - T \text{ average min.}) / 2$

\*\* - other power supplies on request


1 - depth doesn't include 50 mm of power cable, the width does not include the 20 mm of rubber plug

2 - on uniformly loaded surface

3 - reinforced shelf

4 - additional internal glass door

## OPTIONS AND ACCESSORIES




Order number: \*/A

door with viewing window




Order number: \*/P INOX

Stainless steel wire shelf INOX



Order number: \*/PP

Perforated shelf



Order number: \*/PW


Reinforced shelf



**POL-EKO**  
Perfect Environment

(+48) 32 453 91 70  
info@pol-eko.com.pl  
www.pol-eko.com.pl

**POL-EKO A. Polok-Kowalska sp.k.**  
44-300 Wodzisław Śląski  
ul. Kokoszycka 172 C




Order number: KUW GN\*/\*

Stainless steel cuvettes




Order number: QLK\*

Castors



Order number: \*/S or \*/S INOX

Table with castors



Order number: \*/ST or \*/S INOX

Base on castors




Order number: \*/W

Reinforced version



Order number: LabDesk

LabDesk software




Order number: BRT/\*L or IQ/OQ/PQ

Calibration and IQ, OQ, PQ qualification



Order number: \*/3.3

Over temperature protection 3.3 class according to DIN 12880



Order number: BPP 12

Battery backup for display




Order number: PORT ALARM

Dry alarm contact




Order number: LANK

LAN cable




Order number: OCZ/20

Non-standard access port 20 mm




Order number: OCZ/30

Additional access port 30 mm




Order number: OCZ/60

Non-standard access port 60 mm



Order number: OCZ/100

Non-standard access port 100 mm



Order number: KD

Access control