



POL-EKO
Perfect Environment

(+48) 32 453 91 70
info@pol-eko.com.pl
www.pol-eko.com.pl

POL-EKO A. Polok-Kowalska sp.k.
44-300 Wodzisław Śląski
ul. Kokoszycka 172 C

Data sheet


Cooled Incubator (IL) ILW 115 Smart PRO



The photo above is for reference only, may show additional options not included in standard equipment. The real appearance, particularly color and structure of the material may differ from the ones presented in the photo.

Advantages of the SMART PRO controller:

- large (7"), clear, full colour touch screen
- LAN, USB ports and WiFi for communication and data transfer
- multi-segment time and temperature programs
- overview of data in tabular and graphic form
- visual and sound alarm
- Admin function for management
- password protected log-in
- internal memory for programs and data storage
- event registry with user notifications
- LabDesk software and user manual for direct download




Smart PRO - preview screen



1	143
type	ILW 115 Smart PRO
TECHNICAL DATA	
air convection	forced
chamber capacity [l]	112
working capacity [l]	112
controller	microprocessor PID
display	7" full colour touch screen
TEMPERATURE	
temperature range [°C]	0...+100 / -10...+100 (option)
temperature resolution every ... [°C]	0,1
temperature fluctuation at 37°C [±/°C]*	0,2
temperature variation at 37°C [±/°C]*	0,3
temperature protection	class 3.3 to DIN 12880
CHAMBER	
door type	double(5) / door with viewing window (option)
interior	
Smart PRO	acid-proof stainless steel to DIN 1.4301
IG Smart PRO	acid-proof stainless steel to DIN 1.4301
housing	
Smart PRO	powder coated sheet
IG Smart PRO	stainless steel linen finish

overall dims [mm] /1/

width A	660
height B	1140
depth C	720
internal dims [mm]	
width D	460
height E	540
depth F	450



shelves (standard max)	2 7
max shelf workload [kg] /2/	25
- reinforced shelf version (PW) [kg] /3/	50
max unit workload [kg]	60
- reinforced unit version (W) [kg] /4/	120
weight [kg]	90



ELECTRICAL PARAMETERS

voltage**	230V 50-60Hz
nominal power [W]	500
refrigerant	1234ze / GWP=1
warranty	24 months
manufacturer	POL-EKO
txt_opis_pt	<p>all the above technical data refer to standard units (without optional accessories)</p> <p>* - fluctuation measured in centre of the chamber; in space, variation (K) calculated for chamber as: K= +/- (T average max. - T average min.) / 2</p> <p>** - other power supplies on request</p> <p>1 - depth doesn't include 50 mm of power cable, the width does not include the 20 mm of rubber plug</p> <p>2 - on uniformly loaded surface</p> <p>3 - reinforced shelf</p> <p>4 - additional internal glass door</p>
PL typ urządzenia	Cooled Incubator (IL)
img_photo	ILW-115-Smart-PRO
<p>The photo above is for reference only, may show additional options not included in standard equipment. The real appearance, particularly color and structure of the material may differ from the ones presented in the photo.</p>	
nazwa www pl	Inkubator z chłodzeniem ILW 115 Smart PRO
nazwa www EN	Cooled Incubator (IL) ILW 115 Smart PRO
nazwa www ES	Incubadora de Refrigeración (IL) ILW 115 Smart PRO
ekran_grafika	st_il_smart_pro
	Inkubatory Laboratoryjne
0	1

all the above technical data refer to standard units (without optional accessories)

* - fluctuation measured in centre of the chamber; in space, variation (K) calculated for chamber as:
K= +/- (T average max. - T average min.) / 2

** - other power supplies on request


1 - depth doesn't include 50 mm of power cable, the width does not include the 20 mm of rubber plug

2 - on uniformly loaded surface

3 - reinforced shelf

4 - additional internal glass door

OPTIONS AND ACCESSORIES




Order number: */A

door with viewing window




Order number: */P INOX

Stainless steel wire shelf INOX



Order number: */PP

Perforated shelf



Order number: */PW

Reinforced shelf



POL-EKO
Perfect Environment

(+48) 32 453 91 70
info@pol-eko.com.pl
www.pol-eko.com.pl

POL-EKO A. Polok-Kowalska sp.k.
44-300 Wodzisław Śląski
ul. Kokoszycka 172 C




Order number: KUV GN*/*

Stainless steel cuvettes




Order number: QLK*

Castors



Order number: */S or */S INOX

Table with castors



Order number: */ST or */S INOX

Base on castors



Order number: *PLUS

Automatic defrosting function



Order number: */T

Low temperature version




Order number: */W

Reinforced version




Order number: OWW/OWW LED

Interior lighting




Order number: */FIT

Phytotron system




Order number: PT 100

Additional temperature sensor




Order number: GNZ

Internal socket



Order number: BRT*/L or IQ/OQ/PQ

Calibration and IQ, OQ, PQ qualification




Order number: BPP 12

Battery backup for display




Order number: PORT ALARM

Dry alarm contact




Order number: LANK

LAN cable



Order number: OCZ/20

Non-standard access port 20 mm



Order number: OCZ/30

Additional access port 30 mm




Bank: ING BŚ o/Wodzisław Śląski | **Nr rachunku:** 90 1050 1403 1000 0022 0879 5498 | **Nr rej. w BDO** 000005609
NIP: 647-216-26-87 | **REGON:** 276111984 | Sąd Rejonowy w Gliwicach, X Wydział Gospodarczy | **KRS** 0001009595



POL-EKO
Perfect Environment


(+48) 32 453 91 70
info@pol-eko.com.pl
www.pol-eko.com.pl

POL-EKO A.Polok-Kowalska sp.k.
44-300 Wodzisław Śląski
ul. Kokoszycka 172 C



Order number: OCZ/60

Non-standard access port 60 mm



Order number: OCZ/100

Non-standard access port 100 mm



Order number: KD

Access control