

Data sheet

Climatic Chamber with Phytotron System KK 1200 FIT P Smart PRO



The photo above is for reference only, may show additional options not included in standard equipment. The real appearance, particularly color and structure of the material may differ from the ones presented in the photo.

Advantages of the SMART PRO controller:

- large (7"), clear, full colour touch screen
- LAN, USB ports and WiFi for communication and data transfer
- multi-segment time and temperature programs
- overview of data in tabular and graphic form
- visual and sound alarm
- Admin function for management
- password protected log-in
- internal memory for programs and data storage
- event registry with user notifications
- LabDesk software and user manual for direct download



Smart PRO - preview screen

TECHNICAL DATA

air convection	forced
chamber capacity [l]	1330
working capacity [l]	1132
controller	microprocessor PID
display	7" full colour touch screen

TEMPERATURE AND HUMIDITY

temperature range [°C]	0...+60 (with light on +10...+50)
temperature resolution every ... [°C]	0,1
temperature fluctuation at 25°C and 60%rH [°C]	2
relative humidity range [%]	30...90 (see chart for details)
humidity resolution every ... [%]	1,0
humidity fluctuation at 25°C and 60% rH [%rH]	5
over temperature protection	class 3.3 to DIN 12880


CHAMBER


door type	double (external solid, internal glass) / external glass (option)
interior	
Smart PRO	acid-proof stainless steel to DIN 1.4301
IG Smart PRO	acid-proof stainless steel to DIN 1.4301
housing	
Smart PRO	powder coated sheet
IG Smart PRO	stainless steel linen finish

overall dims [mm] /1/

width A	1470
height B	1990
depth C	1060

internal dims [mm]

width D	1270
width D'	1340
height E	1510
depth F	660
height I	1360



shelves (standard max)	2 x 3 11
max shelf workload [kg] /2/	30
- reinforced shelf version (PW) [kg] /3/	100
max unit workload [kg]	300
weight [kg]	220

ELECTRICAL PARAMETERS

voltage*	230V 50Hz
nominal power [W]	4100
refrigerant	R290 / GWP=3
warranty	24 months
manufacturer	POL-EKO-APARATURA

all the above technical data refer to standard units (without optional accessories)

* - other power supplies on request


1 - depth doesn't include 50 mm of power cable

2 - on uniformly loaded surface

3 - reinforced shelf

4 - reinforced version

OPTIONS AND ACCESSORIES




Order number: */A

door with viewing window






Order number: */P INOX

Stainless steel wire shelf INOX



Order number: */PP

Perforated shelf

	Order number: */PW	Reinforced shelf
	Order number: KUW GN*/*	Stainless steel cuvettes
	Order number: FIT/R3	FIT panels independent control
	Order number: PT 100	Additional temperature sensor
	Order number: GNZ	Internal socket
	Order number: OCZ/N	Non-standard access port for external sensor
	Order number: KK/CP	Low water level sensor
	Order number: BRT*/L or IQ/OQ/PQ	Calibration and IQ, OQ, PQ qualification
	Order number: BPP 12	Battery backup for display
	Order number: PORT ALARM	Dry alarm contact