



POL-EKO®

(+48) 32 453 91 70
info@pol-eko.com.pl
www.pol-eko.com.pl

POL-EKO A.Polok-Kowalska sp.k.
44-300 Wodzisław Śląski
ul. Kokoszycka 172 C

Data sheet

print date: 2026-06-15

Stationary sampler
PP 2002+E /12




The photo above is for reference only, may show additional options not included in standard equipment. The real appearance, particularly color and structure of the material may differ from the ones presented in the photo.



| | |
|----------------------------------|--|
| Sampling system | peristaltic pump |
| Sample storing | stable temperature +4°C regardless of ambient conditions |
| Menu language | EN, FR, PL, CZ, RO, LT, IT |
| Medium | liquids of conductivity min 20 µS/cm and max temp. 60°C |
| Hose blowing | before and after sample taking |
| Sampling mode | automatic time proportional, flow proportional, event or manual |
| Sampling height [m] | max 8 |
| Sample volume [ml] | regulated 10...9990 |
| Hose lenght [m] | 8 standard |
| Hose diameter [mm] | 10/15 |
| Distributor | round |
| Number of bottles x capacity [l] | 12 x 2,9 |
| Housing | acid-proof stainless steel with 40 mm insulation |
| Ambient temperature [°C] | -20...+45 |
| Operating conditions | indoor or outdoor installation |
| Controller | microprocessor, graphic display with contrast control, bottle filling overview |
| Programming | 5 programs, 8 tasks each |
| Data logging | SD card + Sampler Viewer software |
| Communication | RS 232 or RS 485 |
| Input signals | 8 analogue, 4 binary |
| Output signals | 4 binary |

overall dims [mm]

| | |
|----------|------|
| Width A | 630 |
| Height B | 1070 |
| Depth C | 660 |



weight [kg] 90

ELECTRICAL PARAMETERS

| | |
|-------------------|-------------|
| voltage | 230 V 50 Hz |
| nominal power [W] | 450 |
| warranty | 24 months |
| manufacturer | POL-EKO® |