



**POL-EKO**  
Perfect Environment

(+48) 32 453 91 70  
info@pol-eko.com.pl  
www.pol-eko.com.pl


**POL-EKO A. Polok-Kowalska sp.k.**  
44-300 Wodzisław Śląski  
ul. Kokoszycka 172 C

## Data sheet

## Drying Oven SLN 53 SIMPLE



The photo above is for reference only, may show additional options not included in standard equipment. The real appearance, particularly color and structure of the material may differ from the ones presented in the photo.





1	81
type	SLN 53 SIMPLE

#### TECHNICAL DATA

air convection	natural
chamber capacity [l]	56
working capacity [l]	56
controller	microprocessor with external display
display	LCD

#### TEMPERATURE

temperature range [°C]	5°C above ambient temperature ... +250°C
temperature resolution every ... [°C]	0,1
temperature protection	class 1.0 to DIN 12880

#### CHAMBER


door type	solid
interior	stainless steel to DIN 1.4016
housing	powder coated sheet

#### overall dims [mm] /1/

width A	660
height B	590
depth C	620

#### internal dims [mm]

width D	390
height E	390
depth F	350



shelves (standard   max)	2   5
max shelf workload [kg] /2/	10
max unit workload [kg]	40
weight [kg]	46



## ELECTRICAL PARAMETERS

voltage**	230V 50-60Hz
nominal power [W]	1700
warranty	24 months
manufacturer	POL-EKO
txt_opis_pt	all the above technical data refer to standard units (without optional accessories) * - fluctuation measured in centre of the chamber; in space, variation (K) calculated for chamber as: $K = \pm (T \text{ average max.} - T \text{ average min.}) / 2$ ** - other power supplies on request 1 - depth doesn't include 50 mm of power cable, the width does not include the 20 mm of rubber plug
PL typ urządzenia	Drying Oven
img_photo	SLN-53-SIMPLE
The photo above is for reference only, may show additional options not included in standard equipment. The real appearance, particularly color and structure of the material may differ from the ones presented in the photo.	
nazwa www pl	Suszarka Laboratoryjna SLN 53 SIMPLE
nazwa www EN	Drying Oven SLN 53 SIMPLE
nazwa www ES	Estufa de Secado SLN 53 SIMPLE
ekran_grafika	simple
	Suszarki Simple
0	1

all the above technical data refer to standard units (without optional accessories)

\* - fluctuation measured in centre of the chamber; in space, variation (K) calculated for chamber as:

$K = \pm (T \text{ average max.} - T \text{ average min.}) / 2$

\*\* - other power supplies on request


1 - depth doesn't include 50 mm of power cable, the width does not include the 20 mm of rubber plug

## OPTIONS AND ACCESSORIES




Order number: \*/P INOX

Stainless steel wire shelf INOX



Order number: \*/PP

Perforated shelf



Order number: BRT/\*/L or IQ/OQ/PQ

Calibration and IQ, OQ, PQ qualification