



Data sheet

print date: 2026-05-12


Drying Oven with nitrogen blow SLWN 15 Smart



The photo above is for reference only, may show additional options not included in standard equipment. The real appearance, particularly color and structure of the material may differ from the ones presented in the photo.

Advantages of the SMART controller:

- 4,3", clear, full colour touch screen
- LAN, USB ports for data transfer
- multi-segment time and temperature programs
- visual and sound alarm
- internal memory for programs and data storage
- event registry
- user manual for direct download
- Quick change of program parameters
- Alarm Bar
- operating with gloves on



Smart - preview screen



TECHNICAL DATA

air convection	forced
chamber capacity [l]	27
working capacity [l]	14
controller	microprocessor PID
display	4,3" full colour touch screen

TEMPERATURE

temperature range [°C]	5°C above ambient temperature ... +300°C
temperature resolution every ... [°C]	0,1
temperature fluctuation at 105°C [+/-°C]*	0,3
temperature variation at 105°C [+/-°C]*	2
temperature protection	class 2.0 to DIN 12880 / class 3.1 (option)

CHAMBER


door type	solid
interior	acid-proof stainless steel to DIN 1.4301
Smart	
housing	
Smart	powder coated sheet

overall dims [mm] /1/

width A	510
height B	553
depth C	470

internal dims [mm]

width D	320
height E	240
depth F	200



shelves (standard max)	1 2
max shelf workload [kg] /2/	10
max unit workload [kg]	20
weight [kg]	31



ELECTRICAL PARAMETERS

voltage	230V 50/60Hz
nominal power [W]	700
warranty	24 months
manufacturer	POL-EKO®

Available models:

SLWN1 the kit includes connections, valves and a laboratory rotameter (which can be calibrated)

SLWN2 the kit includes connections, valves and a tech rotameter (which cannot be calibrated)

type of rotameter must be specified while placing an order (it is not possible to change a technical rotameter into a laboratory one and vice versa)

all the above technical data refer to standard units (without optional accessories)

* - fluctuation measured in centre of the chamber; in space, variation (K) calculated for chamber as:

$K = \pm (T \text{ average max.} - T \text{ average min.}) / 2$

** - other power supplies on request

1 - depth doesn't include 50 mm of power cable

2 - on uniformly loaded surface

3 - reinforced shelf


4 - reinforced version

OPTIONS AND ACCESSORIES



Order number: */P INOX

Stainless steel wire shelf INOX



Order number: */PP

Perforated shelf



Order number: KUW GN*/*

Stainless steel cuvettes




Order number: HEPA

HEPA Clean Air Filter



Order number: LabDesk

LabDesk software




Order number: BRT*/L or IQ/OQ/PQ

Calibration and IQ, OQ, PQ qualification



Order number: */3.1

Over temperature protection 3.1 class according to DIN 12880



Order number: BPP 12

Battery backup for display



Order number: PORT ALARM

Dry alarm contact



POL-EKO®

(+48) 32 453 91 70
info@pol-eko.com.pl
www.pol-eko.com.pl

POL-EKO A.Polok-Kowalska sp.k.
44-300 Wodzisław Śląski
ul. Kokoszycka 172 C



Order number: LANK

LAN cable



Order number: 5-1200-5009-0401001

Solenoid valve SLWN