



POL-EKO
Perfect Environment

(+48) 32 453 91 70
info@pol-eko.com.pl
www.pol-eko.com.pl

POL-EKO A. Polok-Kowalska sp.k.
44-300 Wodzisław Śląski
ul. Kokoszycka 172 C

Data sheet


Cooled Incubator (ST) with freezer ST 2 / ZLN 85 Smart PRO



The photo above is for reference only, may show additional options not included in standard equipment. The real appearance, particularly color and structure of the material may differ from the ones presented in the photo.

Advantages of the SMART PRO controller:

- large (7"), clear, full colour touch screen
- LAN, USB ports and WiFi for communication and data transfer
- multi-segment time and temperature programs
- overview of data in tabular and graphic form
- visual and sound alarm
- Admin function for management
- password protected log-in
- internal memory for programs and data storage
- event registry with user notifications
- LabDesk software and user manual for direct download



Smart PRO - preview screen



TECHNICAL DATA

| | |
|----------------------|-----------------------------|
| air convection | forced / natural |
| chamber capacity [l] | 150 / 85 |
| working capacity [l] | 122 / 73 |
| controller | microprocessor PID |
| display | 7" full colour touch screen |

TEMPERATURE

| | |
|--|------------------------|
| temperature range [°C] | +3...+70 / 0...+15 |
| temperature resolution every ... [°C] | 0,1 |
| temperature fluctuation at 37°C [±/°C]* | 0,3 |
| temperature fluctuation at -20°C [±/°C]* | 0,5 |
| temperature variation at 37°C [±/°C]* | 0,6 |
| temperature variation at -20°C [±/°C]* | 2 |
| temperature protection | class 3.2 to DIN 12880 |

CHAMBER

| | |
|-----------|---|
| door type | solid / glass or double (option) /4/ solid (ZL) |
|-----------|---|

interior

| | |
|--------------|-------------------------------|
| C Smart PRO | stainless steel to DIN 1.4016 |
| CS Smart PRO | stainless steel to DIN 1.4016 |
| P Smart PRO | DIN 1.4301 |
| PS Smart PRO | DIN 1.4301 |

housing


| | |
|--------------|--------------------------|
| C Smart PRO | powder coated sheet |
| CS Smart PRO | stainless steel polished |
| P Smart PRO | powder coated sheet |
| PS Smart PRO | stainless steel polished |

overall dims [mm] /1/

| | |
|----------|------|
| width A | 600 |
| height B | 1720 |
| depth C | 650 |

internal dims [mm]

| | |
|----------|-----------|
| width D | 480 / 380 |
| width D' | 520 / 420 |
| height E | 660 / 590 |
| depth F | 420 / 400 |
| depth F' | 480 / 440 |
| depth G | 320 / 230 |
| height H | 440 / 380 |



| | |
|-----------------------------|---------------|
| shelves (standard max) | 3 4 / 2 4 |
| max shelf workload [kg] /2/ | 10 |
| max unit workload [kg] | 30 / 30 |
| weight [kg] | 116 |



ELECTRICAL PARAMETERS

| | |
|-------------------|--------------------------------|
| voltage** | 230V 50-60Hz |
| nominal power [W] | 500 |
| refrigerant | R1234ze / GWP=7 R290 / GWP=3 |
| warranty | 24 months |
| manufacturer | POL-EKO |

all the above technical data refer to standard units (without optional accessories)

* - fluctuation measured in centre of the chamber; in space, variation (K) calculated for chamber as: $K = \pm (T \text{ average max.} - T \text{ average min.}) / 2$; parameters given for the chamber above the bottom step

** - other power supplies on request


1 - depth doesn't include 50 mm of power cable, the width does not include the 20 mm of rubber plug

2 - on uniformly loaded surface

3 - reinforced shelf


4 - additional internal glass door

OPTIONS AND ACCESSORIES



Order number: */C

Internal glass door




Order number: */A

External glass door




Order number: */P INOX

Stainless steel wire shelf INOX




Order number: */PP

Perforated shelf




Order number: */PW

Reinforced shelf




Order number: KUW GN*/*

Stainless steel cuvettes



Order number: ST/CHL/SWP ALU

Aluminum drawer with powder coated slides



Order number: ST/CHL/SWP INOX

Stainless steel drawer with powder coated slides



Order number: ST/CHL/SWPN INOX

Stainless steel drawer with stainless steel slides



Order number: *PLUS


Automatic defrosting function



POL-EKO
Perfect Environment


(+48) 32 453 91 70
info@pol-eko.com.pl
www.pol-eko.com.pl

POL-EKO A. Polok-Kowalska sp.k.
44-300 Wodzisław Śląski
ul. Kokoszycka 172 C




Order number: ST/70

Extended temperature range to 70°C



Order number: */FOT

Photoperiodic system




Order number: GNZ

Internal socket



Order number: LabDesk

LabDesk software



Order number: BRT/*/L or IQ/OQ/PQ

Calibration and IQ, OQ, PQ qualification



Order number: */3.2

Over temperature protection 3.2 class according to DIN 12880




Order number: BPP 12

Battery backup for display




Order number: PORT ALARM

Dry alarm contact




Order number: LANK

LAN cable




Order number: OCZ/20

Non-standard access port 20 mm




Order number: OCZ/30

Additional access port 30 mm




Order number: OCZ/60

Non-standard access port 60 mm



Order number: OCZ/100

Non-standard access port 100 mm



Order number: KD

Access control